



## Lineman's Crimping Pliers, 9-Inch



The Lineman's Crimping Pliers feature a crimping die behind the hinge. This provides superior leverage when crimping non-insulated connectors, lugs, and terminals. The rivet on these pliers are closer to the cutting edge which provides 46-Percent more cutting and gripping power than other pliers. Induction hardened cutting knives are extra durable for longer life.

### Specifications

<b>Type:</b>	High Leverage Side Cutting/Connector Crimping Pliers	<b>Application:</b>	Cutting and Crimping
<b>Overall Length:</b>	9.33" (23.7 cm)	<b>Material:</b>	Steel
<b>Nose Type:</b>	New England	<b>Jaw Length:</b>	1.594" (4 cm)
<b>Jaw Width:</b>	1.25" (3.2 cm)	<b>Jaw Thickness:</b>	0.625" (1.6 cm)
<b>Jaw Capacity:</b>	1.375" (3.5 cm)	<b>Knife Length:</b>	Yellow
<b>Joint Type:</b>	Locking	<b>Handle Color:</b>	Yellow
<b>Handle Finish:</b>	Plastic-Dipped	<b>Handle Length:</b>	5.563" (14.1 cm)
<b>Insulated:</b>	No	<b>Tether Capable:</b>	No
<b>Weight:</b>	1.0 lb (0.5 kg)		