



## Side Cutting Pliers, New England Insulated, 9-Inch



These Klein Tools Side Cutting New England Insulated Pliers are insulated by two layers and pass both the IEC 60900 and ASTM F1505 standards. They are made of forged steel with induction-hardened knives for strength and durability. And they have high-leverage design which provides 46-percent more cutting and gripping power than other plier designs.

### Specifications

<b>Type:</b>	Side Cutting Pliers	<b>Application:</b>	ACSR, Screws, Nails and Most Hardened Wires
<b>Special Features:</b>	Integral Guards Help Prevent Hand Contact With Conductive Parts	<b>Overall Length:</b>	9.68" (24.6 cm)
<b>Material:</b>	Induction Hardened Steel	<b>Nose Type:</b>	New England
<b>Jaw Length:</b>	1.594" (4 cm)	<b>Jaw Width:</b>	1.25" (3.2 cm)
<b>Jaw Thickness:</b>	0.613" (1.6 cm)	<b>Jaw Capacity:</b>	1.375" (3.5 cm)
<b>Knife Length:</b>	0.797" (2 cm)	<b>Cut Style:</b>	Side-Cutting
<b>Joint Type:</b>	Hot-Riveted	<b>Handle Color:</b>	Orange
<b>Handle Finish:</b>	2-Layer Insulation	<b>Insulated:</b>	Yes
<b>Standards:</b>	IEC 60900 and ASTM F1505	<b>Weight:</b>	1.3 lb (0.6 kg)