



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Veterans Avenue
75672-0000, TX Marshall
Phone: 903-935-9535
Fax: 903-935-3490



D26MR40A D23/D26 Type M Relays&Acc B/G

Eaton Corp

Catalog Number	D26MR40A
Manufacturer	Eaton Corp
Description	Eaton D26 Series Ac Relay, Four-Pole, 120V/60 HZ-110V Coil Voltage, 50 HZ, 4NO Contact Configuration, 0 Blank Cavities
Weight per unit	2.0 (lbs/each)
Product Category	Nema Control Relays & Accy.

Features

Assembly/Kit	Yes
Contact Configuration	4 NO
dimensions	4.0000 IN X 2.3800 IN X 3.5700 IN
Poles	4

Descriptions

Description	D23/D26 TYPE M RELAYS&ACC B/G
extra long description	ETN D26MR40A D23/D26 TYPE M RELAYS&
Features	NEMA machine tool relays include the Freedom 600 V multi-pole (D15), fixed contact industrial control (BF, BFD), convertible contact industrial control (AR, ARD) and type M, multi-pole with convertible contacts (D26). These relays can be ordered as complete devices in any pole combination up to a maximum of 12NO or 8NC and 4NO poles. They are also designed for use on machines, process lines, conveyors and similar automatic and semiautomatic equipment.
Long Description	Eaton D26 Series AC Relay, Four-pole, 120V/60 Hz-110V coil voltage, 50 Hz, 4NO contact configuration, 0 blank cavities
Product Type	D23/D26 Type M Relays&Acc B/G

Manufacturer Information

Brand	Eaton
GTIN	00782113180717
Manufacturers Part Number	D26MR40A
UPC	782113180717

Taxonomies, Classifications, and Categories

Category Description	600V MACHINE TOOL RELAYS
Type	Machine tool relay

Packaging

Carton	1
Weight Per each	1.95



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Veterans Avenue
75672-0000, TX Marshall
Phone: 903-935-9535
Fax: 903-935-3490

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard

CSA file No. LR353,UL Listed Class NKCR2,UL Listed file E1230