

## Adjustable Wrenches – Extra Capacity

Additional Features:

- Extra capacity allows use of a smaller size wrench to handle bigger jobs, especially in confined spaces.
- Forged heat-treated alloy steel for maximum strength and light weight.
- High polish chrome finish.



D507-8

Cat. No.	Handle Finish	Length	Capacity	Weight (lbs.)
507-6	plain	6-1/4" (158 mm)	15/16" (23 mm)	.25
507-8	plain	8-1/4" (209 mm)	1-1/8" (28 mm)	.51
507-10	plain	10-1/4" (260 mm)	1-5/16" (33 mm)	.86
507-12	plain	12-1/4" (311 mm)	1-1/2" (38 mm)	1.32
D507-6	plastic-dipped	6-3/8" (162 mm)	15/16" (23 mm)	.27
D507-8	plastic-dipped	8-3/8" (213 mm)	1-1/8" (28 mm)	.62
D507-10	plastic-dipped	10-3/8" (264 mm)	1-5/16" (33 mm)	1.00
D507-12	plastic-dipped	12-3/8" (315 mm)	1-1/2" (38 mm)	1.54
HD507-6	heavy-duty, plastic-dipped	6-3/8" (162 mm)	15/16" (23 mm)	.27
HD507-8	heavy-duty, plastic-dipped	8-3/8" (213 mm)	1-1/8" (28 mm)	.54
HD507-10	heavy-duty, plastic-dipped	10-3/8" (264 mm)	1-5/16" (33 mm)	1.00
HD507-12	heavy-duty, plastic-dipped	12-3/8" (315 mm)	1-1/2" (38 mm)	1.54

## Adjustable Wrenches – Standard Capacity, Black Finish

Additional Features:

- Forged and heat-treated alloy steel for maximum strength and light weight.
- Industrial black finish for corrosion resistance.



D508-8

Cat. No.	Handle Finish	Length	Capacity	Weight (lbs.)
508-4	plain	4-1/4" (108 mm)	1/2" (12 mm)	.11
508-6	plain	6-1/4" (158 mm)	3/4" (19 mm)	.25
508-8	plain	8-1/4" (209 mm)	15/16" (23 mm)	.51
508-10	plain	10-1/4" (260 mm)	1-1/8" (28 mm)	.86
508-12	plain	12-1/4" (311 mm)	1-5/16" (33 mm)	1.32
508-15	plain	14-7/8" (378 mm)	1-11/16" (42 mm)	2.92
D508-4	plastic-dipped	4-1/2" (114 mm)	1/2" (12 mm)	.13
D508-6	plastic-dipped	6-3/8" (162 mm)	3/4" (19 mm)	.27
D508-8	plastic-dipped	8-3/8" (213 mm)	15/16" (23 mm)	.62
D508-10	plastic-dipped	10-3/8" (264 mm)	1-1/8" (28 mm)	1.00
D508-12	plastic-dipped	12-3/8" (315 mm)	1-5/16" (33 mm)	1.54
D508-15	plastic-dipped	15-1/8" (384 mm)	1-11/16" (42 mm)	3.21

## Adjustable-Head Construction Wrench

- Versatile wrench fits nuts and bolts to 1-1/2" (38 mm).
- Eliminates the need to carry several fixed-size wrenches.
- Forged from select alloy steel with continuous-taper handle.
- Industrial black finish for corrosion resistance.



3239

Cat. No.	Max. Size Capacity	Length	Weight (lbs.)
3239	1-1/2" (38 mm)	16" (406 mm)	2.36

All dimensions are in inches and (millimeters).

**▲WARNING:** Always wear approved eye protection.

**▲WARNING:** Do NOT push or hammer wrench.

**▲WARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

**▲WARNING:** Do NOT extend handle length.




# Adjustable Wrenches

## Features:

**Precision-machined jaws** are individually chosen and assembled by hand for smooth operation.

Available in high-capacity.



## Adjustable Wrenches – Standard Capacity

Additional Features:

- Forged heat-treated alloy steel for maximum strength and light weight.
- High polish chrome finish.



506-8

Cat. No.	Handle Type	Handle Finish	Length	Capacity	Weight (lbs.)
506-4	dovetail	plain	4-1/4" (108 mm)	1/2" (12 mm)	.11
506-6	dovetail	plain	6-1/4" (158 mm)	3/4" (19 mm)	.25
506-8	dovetail	plain	8-1/4" (209 mm)	15/16" (23 mm)	.51
506-10	dovetail	plain	10-1/4" (260 mm)	1-1/8" (28 mm)	.86
506-12	dovetail	plain	12-1/4" (311 mm)	1-5/16" (33 mm)	1.32
506-15	tapered	plain	15-7/8" (403 mm)	1-11/16" (42 mm)	2.92
500-18	tapered	plain	18-1/4" (463 mm)	2-1/16" (52 mm)	4.67
500-24	tapered	plain	24" (610 mm)	2-1/2" (63 mm)	7.76

## Adjustable Wrenches – Standard Capacity, Plastic-Dipped Handles

Additional Features:

- Plastic-dipped handles for added comfort.
- Forged heat-treated alloy steel for maximum strength and light weight.
- High polish chrome finish.



D506-8

Cat. No.	Handle Type	Handle Finish	Length	Capacity	Weight (lbs.)
D506-4	dovetail	plastic-dipped	4-1/2" (114 mm)	1/2" (12 mm)	.13
D506-6	dovetail	plastic-dipped	6-3/8" (162 mm)	3/4" (19 mm)	.27
D506-8	dovetail	plastic-dipped	8-3/8" (213 mm)	15/16" (23 mm)	.62
D506-10	dovetail	plastic-dipped	10-3/8" (264 mm)	1-1/8" (28 mm)	1.00
D506-12	dovetail	plastic-dipped	12-3/8" (315 mm)	1-5/16" (33 mm)	1.44
D506-15	tapered	plastic-dipped	15-1/8" (384 mm)	1-11/16" (42 mm)	3.21
D500-18	tapered	plastic-dipped	18-3/8" (467 mm)	2-1/16" (52 mm)	5.02
D500-24	tapered	plastic-dipped	24-1/4" (616 mm)	2-1/2" (63 mm)	8.26
HD506-4	dovetail	heavy-duty, plastic-dipped	4-1/2" (114 mm)	1/2" (12 mm)	.13
HD506-6	dovetail	heavy-duty, plastic-dipped	6-3/8" (162 mm)	3/4" (19 mm)	.27
HD506-8	dovetail	heavy-duty, plastic-dipped	8-3/8" (213 mm)	15/16" (23 mm)	.62
HD506-10	dovetail	heavy-duty, plastic-dipped	10-3/8" (264 mm)	1-1/8" (28 mm)	1.00
HD506-12	dovetail	heavy-duty, plastic-dipped	12-3/8" (315 mm)	1-5/16" (33 mm)	1.54

All dimensions are in inches and (millimeters).

**▲WARNING:** Always wear approved eye protection.

**▲WARNING:** Do NOT push or hammer wrench.

**▲WARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

**▲WARNING:** Do NOT extend handle length.

