



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



D603PHIV 600W Rotary 3WAY Dimmer Ivory Clam

Lutron

Catalog Number	D603PHIV
Manufacturer	Lutron
Description	Rotary Dimmer With Push On/Off Knob, Incandescent/Halogen, 3-Way, 120V/600W, Clamshell Packaging In Ivory
Weight per unit	0.2400 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Wallbox
amperage rating	UL, CSA
connection	Wire Leads
load	1 PH
Material	Plastic/Metal
operating cycles	Plastic
Poles	1 PH
Voltage Rating	ELBOW FITTING, 316 STAINLESS STEEL MATERIAL; 1/2 INCH SIZE A; 1/2 INCH SIZE B; .5 SIZE A - DECIMAL; .5 SIZE B - DECIMAL; 1/2 SIZE A - FRACTIONAL; 1/2 SIZE B - FRACTIONAL; NUCLEAR, PHARMACEUTICAL INDUSTRY CHEMICAL, PETROCHEMICAL APPLICATION; CAST PROCESS
Wattage	600 A

Dimensions and Weight

Size	Wire Leads
------	------------

Descriptions

Description	600W ROTARY 3WAY DIMMER IVORY CLAM
Long Description	Rotary Dimmer with Push On/Off Knob, Incandescent/Halogen, 3-way, 120V/600W, clamshell packaging in ivory
Product Type	600W 3WY P/P DMR Iv Clamshell
Special Features	Rotary

Manufacturer Information

Brand	Lutron
GTIN	00027557113229
Manufacturers Part Number	D-603PH-IV
sub brand	Rotary
UPC	027557113229

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Lutron



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
--------	---

Package	6
---------	---

Weight Per each	0.24
-----------------	------

Uses, Certifications, and Standards

Application	Dimmer with push on/off knob, 3-way, clamshell packaging
-------------	--

Enclosure	Plastic/Metal
-----------	---------------

environmental conditions	Relative humidity less than 90 percentnon-condensing. Indoor use only
--------------------------	---

Frequency Rating	600 W
------------------	-------

Mounting	WALLBOX
----------	---------

Operating Temperature	Push knob
-----------------------	-----------

standard	UL, CSA
----------	---------