

# Eaton DC1-327D0NB-A20CE1

Catalog Number: DC1-327D0NB-A20CE1

DC1 IP20 240V 3PH IN/3PH OUT 2HP, BR, 7A ENH FW

## General specifications



Photo is representative

### Product Name

Eaton PowerXL DC1 adjustable frequency drive

### Catalog Number

DC1-327D0NB-A20CE1

### UPC

786687020226

### Product Length/Depth

10.25 in

### Product Height

9 in

### Product Width

5.75 in

### Product Weight

4.6 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year cUL Certified from the date of installation of the product or eighteen (18) months from the date of shipment of the product, whichever occurs first. Plus 5 years on capacitor cells.

### Certifications

EN 61800-3  
UkrSepro  
EN 60529  
UL Listed  
EN 61800-5-1

defaultTaxonomyAttributeLabel

Resources

Type

VF drive

Frame

2

Rated operational current

7 A

Catalogs

[Product Datasheet - DC1-327D0NB-A20CE1](#)

Specifications and datasheets

[Eaton Specification Sheet - DC1-327D0NB-A20CE1](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)