

Eaton DC1-344D1NB-A20CE1

Catalog Number: DC1-344D1NB-A20CE1

DC1 IP20 480V IN/460V OUT 2HP, 4.1A, BR, ENH FW

General specifications



Photo is representative

Product Name

Eaton PowerXL DC1 adjustable frequency drive

Catalog Number

DC1-344D1NB-A20CE1

UPC

786687020554

Product Length/Depth

10.25 in

Product Height

9 in

Product Width

5.75 in

Product Weight

4.6 lb

Warranty

Eaton Selling Policy 25-000, one (1) year cUL Certified from the date of installation of the product or eighteen (18) months from the date of shipment of the product, whichever occurs first. Plus 5 years on capacitor cells.

Certifications

EN 61800-3
UkrSepro
EN 60529
UL Listed
EN 61800-5-1

defaultTaxonomyAttributeLabel

Resources

Type

VF drive

Frame

2

Rated operational current

4.1 A

Catalogs

[Product Datasheet - DC1-344D1NB-A20CE1](#)

Specifications and datasheets

[Eaton Specification Sheet - DC1-344D1NB-A20CE1](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)