

Eaton DE1-345D0NN-N20N

Catalog Number: DE1-345D0NN-N20N

Eaton DE1 Variable Speed Starter Modbus IP20 480V Three-phase mains connection/three-phase motor connection 5.0A 3Hp FS2



Photo is representative

General specifications

Product Name	Catalog Number
Eaton PowerXL DE1 variable speed starter	DE1-345D0NN-N20N
	UPC
	786685949062
Product Length/Depth	Product Height
9.09 in	3.54 in
Product Width	Product Weight
6.65 in	3.7 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year CE Marked from the date of installation of the Product or eighteen (18) months from the C-Tick date of shipment of the Product, whichever occurs first.	RoHS Compliant

defaultTaxonomyAttributeLabel

Serial interface

Modbus

User interface

RS-485

Display

None

Enclosure

IP20

Frame

2

Resources

Catalogs

[Product Datasheet - DE1-345D0NN-N20N](#)

Drawings

[DE1_\(FR2\) 2D Drawing Xchange](#)

[DE1_\(FR2\) AutoCAD 2D Footprint](#)

[DE1_\(FR2\) 3D Inventor](#)

[DE1_\(FR2\) AutoCAD 2D Footprint \(mm\)](#)

[DE1_\(FR2\) 2D PDF](#)

[DE1_\(FR2\) 3D Model Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - DE1-345D0NN-N20N](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)