

Specifications



Eaton DF10P-C4

Eaton 0-10V Decorator dimmer 120/277Vac
60hz NO NEUTRAL REQ Side/ Back screw
terminals acpt #14-#12 wire 0-10V wire
leads(purple/grey) recm #16-#18 wire Single
pole/3-way app w/a 3way sw. Presets
Polycarb const-C4-BK,W,V

General specifications

PRODUCT NAME	Eaton decorator dimmer
CATALOG NUMBER	DF10P-C4
UPC	032664736841
PRODUCT LENGTH/DEPTH	2.1 in
PRODUCT HEIGHT	5.9 in
PRODUCT WIDTH	3.8 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	NOM cULus Listed
PRODUCT TYPE	Decorator dimmer

Product specifications

FREQUENCY RATING	60 Hz
SPECIAL FEATURES	Preset feature
TYPE	Dimmer
VOLTAGE RATING	120/277 V
POWER CONSUMPTION	1660 W 1200 W
ILLUMINATION	1000 sq ft coverage
WIRING METHOD	Back and side
ENVIRONMENTAL CONDITIONS	Indoor
SWITCH TYPE	Single-pole, three-way
LOAD TYPE	FLR LED
TORQUE RATING	14 lbf-inch
ACTUATOR	Slide
COLOR	Ivory White Black
CONNECTION TYPE	Screw terminal

Resources

INSTALLATION VIDEOS	How to install Eaton's universal slide dimmers
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - DF10P-C4 Decorator 0-10 volt dimmer spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

