



DFLA25LCYUNV176 216W, 100-277V 3/4" NPT, 7X6 Led FLD *Crouse-Hinds*

Catalog Number	DFLA25LCYUNV176
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Pauluhn Dfla High Lumen Led Floodlight, Cool White, 750-1000W Equivalent Luminaire, Heat and Impact Resistant Glass Lens, 25000 LM, 118 LM/W, Die Cast Aluminum, Yoke, 7X6, PF >0.90, 100-277 Vac, 216W
Weight per unit	32.5 (lbs/each)
Product Category	Lighting

Features

dimensions	15.5000 IN X 7.0000 IN X 12.0000 IN
------------	-------------------------------------

Descriptions

Description	216W,100-277V 3/4" NPT,7X6 LED FLD
extra long description	CRS-H DFLA25LCY/UNV1 76 25K LED DRI
Features	Pauluhn DFL LED floodlights are designed to provide full-spectrum, crisp, white light for maximum visibility. Five versions are available, from 11,000 to 25,000 lumens, providing ideal solutions for a wide range of drilling applications. Primary applications for the DFL LED include outdoor platform and perimeter lighting on land and marine drilling rigs, including derricks, masts, SCR houses, top drives, operator's house, pump and power stations.
Long Description	Eaton Crouse-Hinds series Pauluhn DFLA high lumen LED floodlight, Cool white, 750-1000W equivalent luminaire, Heat and impact resistant glass lens, 25000 lm, 118 lm/W, Die cast aluminum, Yoke, 7x6, PF >0.90, 100-277 Vac, 216W
Product Type	25K Led Drilling Cool Glass Lens 100-277 Vac 127-300 VDC

Manufacturer Information

Brand	Eaton
GTIN	00662276676824
Manufacturers Part Number	DFLA25LCY/UNV1 76
UPC	662276676824

Taxonomies, Classifications, and Categories

Category Description	Led Lighting
Type	FLOODLIGHT

Packaging

Carton	1
Weight Per each	32.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street
72209-0000, AR Little Rock
Phone: 501-565-1785
Fax: 501-565-0827

Uses, Certifications, and Standards

Application

Ind Facilities & Factories - Facility: Lighting and Lighting Controls