

Eaton DFLA25LCY/UNV1 76

Catalog Number: DFLA25LCY/UNV1 76

Eaton Crouse-Hinds series Pauluhn DFLA high lumen LED floodlight, Cool white, 750-1000W equivalent luminaire, Heat and impact resistant glass lens, 25000 lm, 118 lm/W, Die cast aluminum, Yoke, 7x6, PF >0.90, 100-277 Vac, 216W

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Pauluhn DFLA high lumen LED floodlight	DFLA25LCY/UNV1 76
	UPC
	662276676824
Product Length/Depth	Product Height
15.5 in	12 in
Product Width	Product Weight
7 in	32.5 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 2

Class I, Zone 2

Class II, Division 1

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lamp type

LED

Lumens

25000

Lumens per watt

118

Color temperature

Cool white

Mounting Method

Yoke

Voltage rating

100-277 Vac

Frequency rating

50/60 Hz

Optical distribution

7x6

Lens material

Heat and impact resistant glass

Wattage

216W

Equivalent luminaire

750-1000W

Power factor

> 0.90

Material

Die cast aluminum

Resources

Brochures

[Crouse-Hinds Pauluhn DFLA LED High Lumen Floodlights brochure](#)

Catalogs

[Crouse-Hinds Pauluhn DFLA LED High Lumen Floodlights catalog page](#)

Installation instructions

IF 1798 - DFLA LED Luminaires

Specifications and datasheets

Eaton Specification Sheet - DFLA25LCY/UNV1 76



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)