

# DURAFLOOD SPEC 30

**30W LED FLOOD LIGHT**  
175W PAR 38 REPLACEMENT



Lumens	3,300
LED Source	Lumileds 3030
Driver	Mean Well
CCT	3000K, 5000K
CRI	> 80
Beam Angle	120°
Operating Voltage	100 - 277 VAC, 50/60 HZ
Power Consumption	30W
Lifespan	> 50,000 Hours
IP Grade	IP65
Body Construction	Aluminum and Tempered Glass
Dimensions	6.6" x 4.9" x 2.8"
Weight	3.5 lbs

**ORDER CODE** Example **DFS30Y-BRZ-120D5KA-2V**

Fixture	Mount	Housing	Beam Angle	CCT	Voltage
<b>DFS30</b>	<b>K</b> - Knuckle	<b>BRZ</b> - Bronze	<b>120D</b> - 120°	<b>3K</b> - 3000K	<b>A-2V</b> - 100-277 VAC
	<b>T</b> - Trunnion			<b>5K</b> - 5000K	<b>A-4V</b> - 277-480 VAC
	<b>Y</b> - Yoke				