Eaton DG221NRB

Catalog Number: DG221NRB

Eaton General duty cartridge fuse safety switch, 30 A, NEMA 3R, Red painted galvanized steel, Class H fuses, Fusible with neutral, Two-pole, Three-wire, Category: general duty safety switch, 240 V





Catalog Number

Eaton general duty cartridge fuse safety DG221NRB

switch

UPC

782113120317

Product Length/Depth

Product Height

6.88 in

10.81 in

Product Width

Product Weight

6.38 in

6 lb

Warranty

Compliances

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier

from the date of installation of the

Certifications

Product or eighteen (18) months from the

date of shipment of the Product,

UL Listed

whichever occurs first.

Catalog Notes

Maximum hp ratings apply only when dual element fuses are used. 3-Phase hp rating shown is a grounded B phase

rating, UL listed.





Physical Attributes

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Fusible with neutral

Number Of Poles

Two-pole

Number of wires

3

Type

General duty, cartridge fused

Performance Ratings

Amperage Rating

30A

Fuse class provision

Class H fuses

Voltage rating

240V

Miscellaneous

Product Category

General duty safety switch

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Multimedia

Double Up on Safety

Switching Devices Flex Center

Specifications and datasheets

Eaton Specification Sheet - DG221NRB



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.









Eaton.com/socialmedia