# Eaton DG223NRB

# Catalog Number: DG223NRB

Eaton General duty cartridge fuse safety switch, 100 A, NEMA 3R, Painted galvanized steel, Class H fuses, Fusible with neutral, Twopole, Three-wire, Category: general duty safety switch, 240 V



# General specifications

Product Name	Catalog Number
Eaton general duty cartridge fuse safety	DG223NRB
switch	UPC 782113144252
Product Length/Depth	Product Height
7.38 in	19.25 in
Product Width	Product Weight
9.13 in	14 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) yea	r NEC 230.62 (C) Compliant Barrier
from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product,	Certifications UL Listed
whichever occurs first.	Catalog Notes Maximum hp ratings apply only when dual element fuses are used. 3-Phase hp

rating shown is a grounded B phase

rating, UL listed.



# **Physical Attributes**

#### Enclosure

NEMA 3R

#### Enclosure material

Painted galvanized steel

#### Fuse configuration

Fusible with neutral

#### Number Of Poles

Two-pole

#### Number of wires

3

#### Туре

General duty, cartridge fused

## Performance Ratings

Amperage Rating

100A

Fuse class provision

Class H fuses

Voltage rating

240V

# Miscellaneous

Product Category General duty safety switch

## Resources

Catalogs Eaton's Volume 2—Commercial Distribution

Multimedia Switching Devices Flex Center

Double Up on Safety

Specifications and datasheets Eaton Specification Sheet - DG223NRB



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Right Reserved.

Eaton is a registered trademark.

© 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia