

Eaton DG223UGB

Catalog Number: DG223UGB

Eaton General duty non-fusible safety switch, single-throw, 100 A, NEMA 1, Indoor, Painted steel, Two-pole, Two-wire, 240 V



General specifications

Product Name

Eaton general duty non-fusible safety switch

Catalog Number

DG223UGB

UPC

782114731147

Product Length/Depth

7.38 in

Product Height

6.7 in

Product Width

9.13 in

Product Weight

12 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

WARNING! Switch is not approved for service entrance unless a neutral kit is installed.

defaultTaxonomyAttributeLabel

Type

Non-fusible, single-throw

Amperage Rating

100A

Number Of Poles

Two-pole

Product Category

General duty safety switch

Voltage rating

240V

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse configuration

Non-fusible

Number of wires

2

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DG223UGB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)