

Eaton DG323NGB

Catalog Number: DG323NGB

Eaton General duty cartridge fuse safety switch, 100 A, 240 V, NEMA 1, Painted steel, Class H fuses, Fusible with neutral, Three-pole, Four-wire, Category: general duty safety switch



General specifications

Product Name

Eaton general duty cartridge fuse safety switch

Catalog Number

DG323NGB

UPC

782113144344

Product Length/Depth

7.38 in

Product Height

18.81 in

Product Width

9.13 in

Product Weight

14 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

Maximum hp ratings apply only when dual element fuses are used

Physical Attributes

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type

General duty, cartridge fused

Performance Ratings

Amperage Rating

100A

Fuse class provision

Class H fuses

Voltage rating

240V

Miscellaneous

Product Category

General duty safety switch

Resources

Catalogs

[Switching devices catalog](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DG323NGB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)