

# Eaton DG324UGK

Catalog Number: DG324UGK

Eaton General duty non-fusible safety switch, single-throw, 200 A, NEMA 1, Indoor, Painted steel, Three-pole, Three-wire, 240 V



## General specifications

**Product Name** [Catalog Number](#)

Eaton general duty non-fusible safety switch [DG324UGK](#)

[UPC](#)

782113213552

**Product Length/Depth**

11.25 in

**Product Height**

24.75 in

**Product Width**

16 in

**Product Weight**

48 lb

**Warranty**

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Compliances**

[Certifications](#)

UL Listed

[Catalog Notes](#)

WARNING! Switch is not approved for service entrance unless a neutral kit is installed.

## Type

Non-fusible, single-throw

## Amperage Rating

200A

## Number Of Poles

Three-pole

## Product Category

General duty safety switch

## Voltage rating

240V

## Enclosure

NEMA 1

## Enclosure material

Painted steel

## Fuse configuration

Non-fusible

## Number of wires

3

## Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

## Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

## Specifications and datasheets

[Eaton Specification Sheet - DG324UGK](#)

## Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)