Eaton DG325NGK

Catalog Number: DG325NGK

General specifications

Eaton General duty cartridge fuse safety switch, 400 A, NEMA 1, Painted steel, Class H fuses, Fusible with neutral, Three-pole, Four-wire, Category: general duty safety switch, 240 V

Photo is representative

Product Name	Catalog Number
Eaton general duty cartridge fuse safety switch	DG325NGK
	UPC
	782113639208
	702113033200
Product Length/Depth	Product Height
7.27 in	44.74 in
Product Width	Product Weight
23.08 in	120 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) yea	r NEC 230.62 (C) Compliant Barrier
from the date of installation of the Product or eighteen (18) months from the	Certifications
date of shipment of the Product,	UL Listed
whichever occurs first.	Catalog Notes
	Maximum hp ratings apply only when
	dual element fuses are used



Physical Attributes

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Туре

General duty, cartridge fused

Performance Ratings

Amperage Rating

400A

Fuse class provision

Class H fuses

Voltage rating

240V

Miscellaneous

Product Category General duty safety switch

Resources

Catalogs Eaton's Volume 2—Commercial Distribution

Multimedia Double Up on Safety Switching Devices Flex Center

Specifications and datasheets Eaton Specification Sheet - DG325NGK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Right Reserved.

Eaton is a registered trademark.

© 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia