# Eaton DG325URK

## Catalog Number: DG325URK

Eaton General duty non-fusible safety switch, single-throw, 400 A, NEMA 3R, Rainproof, Painted galvanized steel, Three-pole, Three-wire, 240 V

#### General specifications



Catalog Number

Eaton general duty non-fusible safety

DG325URK

switch

**UPC** 

782113589541

Product Length/Depth

Product Height

7.27 in

44.74 in

Product Width

Product Weight

23.08 in

....

120 lb

Warranty Compliances

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

**UL Listed** 

whichever occurs first.

Catalog Notes

Drilled to accept field installed neutral

kits





### default Taxonomy Attribute Label

Type

Non-fusible, single-throw

**Amperage Rating** 

400A

**Number Of Poles** 

Three-pole

**Product Category** 

General duty safety switch

Voltage rating

240V

Enclosure

NEMA 3R

**Enclosure material** 

Painted galvanized steel

Fuse configuration

Non-fusible

Number of wires

3

#### Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Multimedia

Switching Devices Flex Center

Double Up on Safety

Specifications and datasheets

Eaton Specification Sheet - DG325URK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia