



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DGLC200ANC 2CHNL 20A Dig T-SW

Nsi Industries

Catalog Number	DGLC200ANC
Manufacturer	Nsi Industries
Description	Time Switch, 7 Day Time Setting Mode, 2 Channels, SPDT Contact Form, 7 Day Time Setting, 120 to 277 V Ac, 20 A (No);10 A (NC) @ 120/277 Vac (Ballast);15 A (No) @ 120 V Ac (Tungsten);20 A (No);10 A (NC) @ 24 to 277 V Ac/28 V DC (Resistive), Noryl Enclosure Material, Screw Connection, -31 °F Operating Temperature, +131 °F Operating Temperature, 1.78 LB
Weight per unit	1.8 (lbs/each)
Product Category	Electronic Time Switches

Features

action	SPDT
Base	Screw
Contact Rating	120-277 VAC
Phase	Single Phase
Poles	1
Timing Range	7 DAY

Dimensions and Weight

Size	L=5.000 - H=9.125 - W=4.500
------	-----------------------------

Descriptions

Description	2CHNL 20A DIG T-SW
extra long description	TORK DGLC200A-NC Astronomic Digital
Special Features	SPDT 2 Channel 7 Day Digital Lighting Control Time Switch

Manufacturer Information

GTIN	00786261822130
UPC	786261822130

Taxonomies, Classifications, and Categories

Type	7 Day Lighting Control Time Switch
------	------------------------------------

Packaging

Carton	1
Weight Per each	1.78



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	NEMA 3R Noryl Indoor-Outdoor With Clear Lexan Cover
environmental conditions	-31 to + 131 F
Frequency Rating	50-60 Hz
Mounting	Screw Mount
standard	cULus