

Eaton DH162URKN

Catalog Number: DH162URKN

Eaton DC disconnect, Single-throw, 60 A, NEMA 3R, Painted galvanized steel, Class R fuses, Non-Fusible, Single-pole, One-wire

General specifications



Photo is representative

Product Name

Eaton DC disconnect

Catalog Number

DH162URKN

UPC

786685375700

Product Length/Depth

10 in

Product Height

15.81 in

Product Width

8.87 in

Product Weight

16 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Special features

Neutral assemblies factory installed

Type

Single-throw

Amperage Rating

60 A

Number of circuits

1

Protection

Non-fusible

Number of poles

Single-pole

Voltage rating

600 VDC

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Protection

Non-fusible

Resources

Brochures

[DC disconnects for 600VDC solar photovoltaic installations \(single circuit\)](#)

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DH162URKN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)