Eaton DH221FRK

Catalog Number: DH221FRK

Eaton Heavy duty single-throw fused safety switch, Enhanced visible blade, 30 A, NEMA 3R, Painted galvanized steel, Class H, Fusible without neutral, Two-pole, Two-wire, 240 V, Max Hp: 1.5, 5 hp (1PH @240V/250 Vdc), #14-#2 Cu/Al

General specifications



Eaton heavy duty fusible safety switch

UPC

786685176741

Product Height

7.5 in

Product Weight

14 lb

Catalog Number

DH221FRK

Product Length/Depth

18 in

Product Width

9.5 in

Warranty

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Photo is representative

Certifications

UL Listed



Physical Attributes

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

Number Of Poles

Two-pole

Number of wires

2

Type

Heavy duty fusible safety switch

Performance Ratings

Amperage Rating

30A

HP rating - max

1.5, 5 hp (1PH @240V/250 Vdc)

NEMA rating

NEMA 3R

Voltage rating

240V

Miscellaneous

Product Category

Heavy Duty, Fusible without neutral

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH221FRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia