

# Eaton DH223FRK

Catalog Number: DH223FRK

Eaton Heavy duty single-throw fused safety switch, Enhanced visible blade, 100 A, NEMA 3R, Painted galvanized steel, Two-pole, Two-wire, 240 V, Max Hp: 7.5, 15 hp/15, 30 hp/20 hp (1,3PH @ Std fuse/time delay/250 Vdc), #14-#1/0 Cu/Al

## General specifications



Photo is representative

### Product Name

Eaton heavy duty fusible safety switch

### Catalog Number

DH223FRK

### UPC

786685176765

### Product Length/Depth

22.5 in

### Product Height

9 in

### Product Width

12.75 in

### Product Weight

26 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Physical Attributes

### Enclosure

NEMA 3R

### Enclosure material

Painted galvanized steel

### Fuse class provision

Class H

### Fuse configuration

Fusible without neutral

### Number Of Poles

Two-pole

### Number of wires

2

### Type

Heavy duty fusible safety switch

## Performance Ratings

### Amperage Rating

100A

### HP rating - max

7.5, 15 hp/15, 30 hp/20 hp (1,3PH @ Std fuse/time delay/250 Vdc)

### NEMA rating

NEMA 3R

### Voltage rating

240V

## Miscellaneous

### Product Category

Heavy Duty, Fusible without neutral

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - DH223FRK](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)