# Eaton DH223NRK

# Catalog Number: DH223NRK

Eaton Heavy duty single-throw fused safety switch, Enhanced visible blade, 100 A, NEMA 3R, Neutral, Two-pole, Three-wire, 240 V, Max Hp: 7.5, 15 hp/15, 30 hp/20 hp (1,3PH @ Std fuse/time delay/250 Vdc), #14-#1/0 Cu/Al

# General specifications

Product Name Catalog Number Eaton heavy duty fusible safety switch DH223NRK UPC Product Length/Depth 782113206233 22.5 in Product Width **Product Height** 9 in 12.75 in **Product Weight** Warranty 26 lb Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. Certifications **Catalog Notes** UL Listed 3-Phase hp ratings shown are grounded

B phase ratings; UL listed



Photo is representative



# **Physical Attributes**

#### Enclosure

NEMA 3R

Enclosure material Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible with neutral

Number Of Poles

Two-pole

Number of wires

Туре

Heavy duty fusible safety switch

# Performance Ratings

Amperage Rating

100A

HP rating - max 7.5, 15 hp/15, 30 hp/20 hp (1,3PH @ Std fuse/time delay/250 Vdc)

NEMA rating NEMA 3R

Voltage rating

240V

# Miscellaneous

## Product Category

Heavy Duty, Fusible with neutral

## Resources

Catalogs Eaton's Volume 2—Commercial Distribution

Specifications and datasheets Eaton Specification Sheet - DH223NRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

© 2024 Eaton. All Rights Reserved. All other trademarks are owners.



Eaton.com/socialmedia