

# Eaton DH224NRK

Catalog Number: DH224NRK

Eaton Heavy duty single-throw fused safety switch, Enhanced visible blade, line/load labels, 2 blade, 200 A, NEMA 3R, Cartridge, Three-wire, 240 V, Max Hp: 15, 25 hp/15, 60 hp/40 hp (1,3PH @ Std fuse/time delay/250 Vdc), #6-250 kcmil Cu/Al



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy duty fusible safety switch	DH224NRK
<b>UPC</b>	<b>Product Length/Depth</b>
782113206653	27.6 in
<b>Product Height</b>	<b>Product Width</b>
6.14 in	15.91 in
<b>Product Weight</b>	<b>Warranty</b>
35 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed	3-Phase hp ratings shown are grounded B phase ratings; UL listed

## Physical Attributes

### Enclosure

NEMA 3R

### Enclosure material

Painted galvanized steel

### Fuse class provision

Cartridge

### Fuse configuration

Fusible with neutral

### Number Of Poles

Two-pole

### Number of wires

3

### Type

Heavy duty fusible safety switch

## Performance Ratings

### Amperage Rating

200A

### HP rating - max

15, 25 hp/15, 60 hp/40 hp (1,3PH @ Std fuse/time delay/250 Vdc)

### NEMA rating

NEMA 3R

### Voltage rating

240V

## Miscellaneous

### Product Category

Heavy Duty, Fusible with neutral

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - DH224NRK](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)