Eaton DH227NRK

Catalog Number: DH227NRK

Eaton Heavy duty single-throw fused safety switch, Enhanced visible blade, 800 A, NEMA 3R, Painted galvanized steel, Class L, Two-pole, Three-wire, 240 V, Max Hp: 100, 250 hp (3PH @ Std fuse/time delay), (4)#1/0-(4)750 kcmil Al

General specifications

Product Name

. . . _

Eaton heavy duty fusible safety switch

DH227NRK

Catalog Number

UPC

Product Length/Depth

782113589671

65 in

Product Height

Product Width

13 in

27 in

Product Weight

Warranty

175 lb

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Compliances

Certifications

NEC 230.62 (C) Compliant Barrier

UL Listed

Catalog Notes

3-Phase hp ratings shown are grounded

B phase ratings; UL listed





Photo is representative

Physical Attributes

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse class provision

Class L

Fuse configuration

Fusible with neutral

Number Of Poles

Two-pole

Number of wires

3

Type

Heavy duty fusible safety switch

Performance Ratings

Amperage Rating

800A

HP rating - max

100, 250 hp (3PH @ Std fuse/time delay)

NEMA rating

NEMA 3R

Voltage rating

240V

Miscellaneous

Product Category

Heavy Duty, Fusible with neutral

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH227NRK

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia