



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH261UGK 30A/2P HD NF Safety Switch 600V Nema 1

Eaton Corp

Catalog Number	DH261UGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Non-Fused Safety Switch, Single-Throw, 30 A, Nema 1, Painted Steel, Non-Fusible, Two-Pole, Two-Wire, 3 At 240 Vac TD 1 PH, 7.5 At 480 Vac TD 1 PH, 10 At 600 Vac TD 1 PH, 15 At 600 VDC
Weight per unit	17.0 (lbs/each)
Product Category	Non-Fusible Heavy Duty Safety

### Features

amperage rating	30A
dimensions	9.8900 IN X 8.8100 IN X 15.8100 IN
Material	Painted Steel
media	Yes
Poles	Two-pole
Voltage Rating	600 V

### Descriptions

Description	30A/2P HD NF SAFETY SWITCH 600V NEMA 1
extra long description	ETN DH261UGK 30A/2P HD NF Sfty Sw 6
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 30 A, NEMA 1, Painted steel, Non-Fusible, Two-pole, Two-wire, 3 at 240 Vac TD 1 Ph, 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 15 at 600 Vdc
Product Type	30A/2P HD NF Sfty SW 600V N1

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113205472
Manufacturers Part Number	DH261UGK
UPC	782113205472

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Non-Fusible Safety Switch

### Packaging

Carton	1
Weight Per each	17



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Power

Distribution and Controls

nema rating

NEMA 1

standard

UL Listed, NEC 230.62 (C) Compliant Barrier