Eaton DH261UGK

Catalog Number: DH261UGK

Eaton Heavy duty single-throw non-fused safety switch, Singlethrow, 30 A, NEMA 1, Painted steel, Non-Fusible, Two-pole, Twowire, 3 at 240 Vac TD 1 Ph, 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 15 at 600 Vdc

General specifications

Product Name

Catalog Number

Eaton heavy duty non-fusible safety

DH261UGK

switch

UPC

782113205472

Product Length/Depth

Product Height

9.89 in

15.81 in

Product Width

Product Weight

8.81 in

17 lb

Warranty

Compliances

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier

from the date of installation of the

Certifications

Product or eighteen (18) months from the

date of shipment of the Product,

UL Listed

whichever occurs first.

Catalog Notes

Suitable for service entrance use with a neutral or ground lug kit installed



Photo is representative



Physical Attributes

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse configuration

Non-fusible

Number Of Poles

Two-pole

Number of wires

2

Type

Single-throw

Performance Ratings

Amperage Rating

30A

HP rating - max

3 at 240 Vac TD 1 Ph, 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 15 at 600 Vdc

NEMA rating

NEMA 1

Voltage rating

600 V

Miscellaneous

Product Category

Heavy Duty, Non-Fusible

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH261UGK



Reserved.

Eaton Corporation plc

Eaton House

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.









Eaton.com/socialmedia

