Eaton DH261URK

Catalog Number: DH261URK

General specifications

Eaton Heavy duty single-throw non-fused safety switch, Singlethrow, 30 A, NEMA 3R, Painted galvanized steel, Non-Fusible, Two-pole, Two-wire, 3 at 240 Vac TD 1 Ph, 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 15 at 600 Vdc

Photo is representative

Product Name Catalog Number DH261URK Eaton heavy duty non-fusible safety switch UPC 786685176635 Product Length/Depth **Product Height** 9.89 in 15.81 in **Product Width Product Weight** 8.87 in 17 lb Warranty Compliances Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Certifications Product or eighteen (18) months from the UL Listed date of shipment of the Product, whichever occurs first.



Physical Attributes	Performance Ratings
Enclosure	Amperage Rating
NEMA 3R	30A
Enclosure material	HP rating - max
Painted galvanized steel	3 at 240 Vac TD 1 Ph, 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac
Fuse configuration	TD 1 Ph, 15 at 600 Vdc
Non-fusible	NEMA rating
Number Of Poles	NEMA 3R
Two-pole	Voltage rating
Number of wires	600 V
Туре	Miscellaneous
Single-throw	Product Category
	Heavy Duty, Non-Fusible

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH261URK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Right Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia