Eaton DH262FRK

Catalog Number: DH262FRK

Eaton Enhanced visible blade single-throw safety switch, 60 A, NEMA 3R, Painted galvanized steel, Class H, Fusible without neutral, Two-pole, Two-wire, 600 V, Max Hp: 20, 25 hp/25 hp (1PH @480,600 V TD/600 Vdc), #14-#2 Cu/Al

General specifications



Eaton heavy duty fusible safety switch

UPC

786685177137

Product Height

16.27 in

Product Weight

18 lb

Catalog Number

DH262FRK

Product Length/Depth

17 in

Product Width

9.5 in

Warranty

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Photo is representative

Certifications

UL Listed



Physical Attributes

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

Number Of Poles

Two-pole

Number of wires

2

Type

Heavy duty fusible safety switch

Wire size

#14-2 AWG Cu/AI

Performance Ratings

Amperage Rating

60A

HP rating - max

20, 25 hp/25 hp (1PH @480,600 V TD/600 Vdc)

NEMA rating

NEMA 3R

Voltage rating

600 V

Miscellaneous

Product Category

Heavy Duty, Fusible without neutral

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH262FRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia