Eaton DH321FGK

Catalog Number: DH321FGK

Eaton Enhanced visible blade single-throw safety switch, 30 A, NEMA 1, Painted steel, Class H, Fusible without neutral, Three-pole, Three-wire, 240 V, Max Hp: 1.5, 3/3, 7.5/5 hp (1,3PH @Std/TD, 250 Vdc), #14-#2 Cu/Al

General specifications



Eaton heavy duty fusible safety switch

UPC

782113208510

Product Height

16 in

Product Weight

13 lb

Catalog Number

DH321FGK

Product Length/Depth

16.5 in

Product Width

9.5 in

Warranty

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Certifications

UL Listed

Catalog Notes

Suitable for service entrance use with a

Neutral Kit installed





Photo is representative

Physical Attributes

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

Heavy duty fusible safety switch

Wire size

#14-2 AWG Cu/AI

Performance Ratings

Amperage Rating

30A

HP rating - max

1.5, 3/3, 7.5/5 hp (1,3PH @Std/TD, 250 Vdc)

NEMA rating

NEMA 1

Voltage rating

240V

Miscellaneous

Product Category

Heavy Duty, Fusible without neutral

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH321FGK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia