# Eaton DH321FRK

## Catalog Number: DH321FRK

Eaton Enhanced visible blade single-throw safety switch, 30 A, NEMA 3R, Painted galvanized steel, Class H, Fusible without neutral, Three-pole, Three-wire, 240 V, Max Hp: 1.5, 3/3, 7.5/5 hp (1,3PH @Std/TD, 250 Vdc), #14-#2 Cu/Al

### General specifications



Eaton heavy duty fusible safety switch

DH321FRK

**UPC** 

782113208497

16.5 in

**Product Width** 

Catalog Number

Product Length/Depth

**Product Height** 

16.27 in

9.5 in

**Product Weight** 

Warranty

10 lb

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Certifications **UL** Listed

Suitable for service entrance use with a

Neutral Kit installed

**Catalog Notes** 





#### **Physical Attributes**

Enclosure

NEMA 3R

**Enclosure material** 

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

**Number Of Poles** 

Three-pole

Number of wires

3

Type

Heavy duty fusible safety switch

Wire size

#14-2 AWG Cu/AI

#### Performance Ratings

Amperage Rating

30A

HP rating - max

1.5, 3/3, 7.5/5 hp (1,3PH @Std/TD, 250 Vdc)

**NEMA** rating

NEMA 3R

Voltage rating

240V

#### Miscellaneous

**Product Category** 

Heavy Duty, Fusible without neutral

#### Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH321FRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia