# Eaton DH321NRK

# Catalog Number: DH321NRK

Eaton Enhanced visible blade single-throw safety switch, 30 A, NEMA 3R, Painted galvanized steel, Class H, Fusible with neutral, Three-pole, Four-wire, 240 V, Max Hp: 1.5, 3/ 3, 7.5/ 5 hp (1,3PH @Std/TD, 250 Vdc), #14-#2 Cu/Al

> Catalog Number DH321NRK

## General specifications

Product Name Eaton heavy duty fusible safety switch

UPC 782113205373

Product Height 16.27 in

Product Weight 14.11 lb Product Length/Depth 16.5 in Product Width 9.5 in Warranty Eaton Selling Policy 25-000, one (1) year

from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.



Photo is representative

Certifications UL Listed



# **Physical Attributes**

#### Enclosure

NEMA 3R

Enclosure material Painted galvanized steel

Fuse class provision

Class H

Fuse configuration Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type Heavy duty fusible safety switch

Wire size #14-2 AWG Cu/AI

# Performance Ratings

Amperage Rating

30A

HP rating - max 1.5, 3/ 3, 7.5/ 5 hp (1,3PH @Std/TD, 250 Vdc)

NEMA rating NEMA 3R

Voltage rating

240V

## **Miscellaneous**

Product Category Heavy Duty, Fusible with neutral

# Resources

Catalogs Eaton's Volume 2—Commercial Distribution

Specifications and datasheets Eaton Specification Sheet - DH321NRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Right Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia