



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH322FGK 60A/3P HD Fusible Safety Switch 240V Nema 1

Eaton Corp

Catalog Number	DH322FGK
Manufacturer	Eaton Corp
Description	Eaton Enhanced Visible Blade Single-Throw Safety Switch, 60 A, Nema 1, Painted Steel, Class H, Three-Pole, Three-Wire, 240 V, Max HP: 3, 7.5/ 10, 15/ 10 HP (1, 3PH @STD/TD/250 VDC), #14-#2 Cu/Al
Weight per unit	14.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	60A
dimensions	16.5000 IN X 9.5000 IN X 16.0000 IN
Material	Painted Steel
media	Yes
Poles	Three-pole
Voltage Rating	240V

Dimensions and Weight

Depth	16.5000
Height	16.0000
Width	9.5000

Descriptions

Description	60A/3P HD FUSIBLE SAFETY SWITCH 240V NEMA 1
extra long description	ETN DH322FGK 60A/3P HD Fusible Sfty
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Enhanced visible blade single-throw safety switch, 60 A, NEMA 1, Painted steel, Class H, Three-pole, Three-wire, 240 V, Max Hp: 3, 7.5/ 10, 15/ 10 hp (1,3PH @Std/TD/250 Vdc), #14-#2 Cu/Al
Product Type	60A/3P HD Fusible Sfty SW 240V N1

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113205809
Manufacturers Part Number	DH322FGK
UPC	782113205809



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Fusible safety switch

Packaging

Carton 1

Weight Per each 14

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

nema rating NEMA 1

standard UL Listed