

# Eaton DH322FRK

Catalog Number: DH322FRK

Eaton Enhanced visible blade single-throw safety switch, 60 A, NEMA 3R, Painted galvanized steel, Class H, Three-pole, Three-wire, 240 V, Max Hp: 3, 7.5/ 10, 15/ 10 hp (1,3PH @ Std/TD/250 Vdc), #14-#2 Cu/Al

## General specifications



Photo is representative

### Product Name

Eaton heavy duty fusible safety switch

### Catalog Number

DH322FRK

### UPC

782113205816

### Product Length/Depth

16.5 in

### Product Height

16.27 in

### Product Width

9.5 in

### Product Weight

14 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

### Catalog Notes

Suitable for service entrance use with a Neutral Kit installed

## Physical Attributes

### Enclosure

NEMA 3R

### Enclosure material

Painted galvanized steel

### Fuse class provision

Class H

### Fuse configuration

Fusible without neutral

### Number Of Poles

Three-pole

### Number of wires

3

### Type

Heavy duty fusible safety switch

### Wire size

#14-2 AWG Cu/Al

## Performance Ratings

### Amperage Rating

60A

### HP rating - max

3, 7.5/ 10, 15/ 10 hp (1,3PH @Std/TD/250 Vdc)

### NEMA rating

NEMA 3R

### Voltage rating

240V

## Miscellaneous

### Product Category

Heavy Duty, Fusible without neutral

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - DH322FRK](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)