# Eaton DH323FRK

## Catalog Number: DH323FRK

Eaton Enhanced visible blade single-throw safety switch, 100 A, NEMA 3R, Painted galvanized steel, Class H, Fusible without neutral, Three-pole, Three-wire, 240 V, Max Hp: 7.5, 15/ 15, 30/ 20 hp (1,3PH @Std/TD/250 Vdc), #14-#1/0 Cu/Al

#### General specifications

UPC

9 in

**Product Name** Catalog Number DH323FRK Eaton heavy duty fusible safety switch Product Length/Depth 782113206257 22.5 in Product Width **Product Height** 12.75 in **Product Weight** Warranty 25 lb Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. Certifications **Catalog Notes** UL Listed Suitable for service entrance use with a Neutral Kit installed



### **Physical Attributes**

#### Enclosure

NEMA 3R

Enclosure material Painted galvanized steel

Fuse class provision Class H

Fuse configuration Fusible without neutral

Number Of Poles Three-pole

Number of wires

3

Type Heavy duty fusible safety switch

Wire size #14-1/0 AWG Cu/AI

#### Performance Ratings

Amperage Rating

100A

HP rating - max 7.5, 15/ 15, 30/ 20 hp (1,3PH @Std/TD/250 Vdc)

NEMA rating NEMA 3R

Voltage rating

240V

#### Miscellaneous

Product Category Heavy Duty, Fusible without neutral

#### Resources

Catalogs Eaton's Volume 2—Commercial Distribution

Specifications and datasheets Eaton Specification Sheet - DH323FRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Right Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia