# Eaton DH323NDK

# Catalog Number: DH323NDK

Eaton Heavy duty single-throw fused safety switch, 100 A, NEMA 12/3R, Painted galvanized steel, Class H, Fusible with neutral, Three-pole, Four-wire, 240 V, Max Hp: 7.5, 15/ 15, 30/ 20 hp (1,3PH @Std/TD/250 Vdc), #14-#1/0 Cu/AI

# General specifications



Eaton heavy duty fusible safety switch

**UPC** 

782113206332

**Product Height** 

24.95 in

**Product Weight** 

30 lb

Catalog Number

DH323NDK

Product Length/Depth

10.22 in

**Product Width** 

10.76 in

Warranty

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Compliances

NEC 230.62 (C) Compliant Barrier

Certifications

**UL Listed** 

**Catalog Notes** 

Can be field modified to meetNEMA 3R rainproof requirements when a factory provided drain hole is opened



Photo is representative



# **Physical Attributes**

**Enclosure** 

NEMA 12, NEMA 3R

**Enclosure material** 

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible with neutral

**Number Of Poles** 

Three-pole

Number of wires

Type

Heavy duty fusible safety switch

Wire size

#14-1/0 AWG Cu/AI

### Performance Ratings

**Amperage Rating** 

100A

HP rating - max

7.5, 15/ 15, 30/ 20 hp (1,3PH @Std/TD/250 Vdc)

**NEMA** rating

**NEMA 12/3R** 

Voltage rating

240V

### Miscellaneous

**Product Category** 

Heavy Duty, Fusible with neutral

### Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH323NDK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia