Eaton DH323NGK

Catalog Number: \$headerCatlogNumber

Eaton Heavy duty single-throw fused safety switch, 100 A, NEMA 1, Painted steel, Class H, Fusible, Neutral, Three-pole, Four-wire, 240 V, Max Hp: 7.5, 15/15, 30/20 hp (1,3PH @Std/TD/250 Vdc), #14-#1/0 Cu/Al

Physical Attributes

Enclosure material

NEMA 1 Painted steel

Fuse class provision Fuse configuration

Class H Fusible with neutral

Number Of Poles Number of wires

Three-pole

Type Wire size

Heavy duty fusible safety switch #14-1/0 AWG Cu/Al



Performance Ratings

Amperage Rating

100A

HP rating - max

7.5, 15/15, 30/20 hp (1,3PH @Std/TD/250 Vdc)

NEMA rating

NEMA 1

Voltage rating

240V

Miscellaneous

Product Category

Heavy Duty, Fusible with neutral

Resources

Catalogs

Switching devices catalog

Specifications and datasheets

Eaton Specification Sheet - DH323NGK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia