Eaton DH323NRK

Catalog Number: DH323NRK

Eaton Enhanced visible blade single-throw safety switch, 100 A, NEMA 3R, Painted galvanized steel, Class H, Fusible with neutral, Three-pole, Four-wire, 240 V, Max Hp: 7.5, 15/ 15, 30/ 20 hp (1,3PH @Std/TD/250 Vdc), #14-#1/0 Cu/Al

General specifications

Product Name

Eaton heavy duty fusible safety switch

782113206271

Product Height

9 in

UPC

Product Weight

20 lb

Catalog Number

DH323NRK

Product Length/Depth

22.5 in

Product Width

12.75 in

Warranty

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Certifications

UL Listed



Physical Attributes

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

Type

Heavy duty fusible safety switch

Wire size

#14-1/0 AWG Cu/AI

Performance Ratings

Amperage Rating

100A

HP rating - max

7.5, 15/ 15, 30/ 20 hp (1,3PH @Std/TD/250 Vdc)

NEMA rating

NEMA 3R

Voltage rating

240V

Miscellaneous

Product Category

Heavy Duty, Fusible with neutral

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH323NRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia