

Eaton DH324NRK

Catalog Number: DH324NRK

Eaton Enhanced visible blade single-throw safety switch, 200 A, NEMA 3R, Painted galvanized steel, Class H, Neutral, Three-pole, Four-wire, 240 V, #6-250 kcmil Cu/Al



General specifications

Product Name	Catalog Number
Eaton heavy duty fusible safety switch	DH324NRK
UPC	Product Length/Depth
782113206691	10 in
Product Height	Product Width
28.12 in	15.52 in
Product Weight	Warranty
52 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

Physical Attributes

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type

Heavy duty fusible safety switch

Wire size

#6 AWG-250 kcmil Cu/Al

Performance Ratings

Amperage Rating

200A

HP rating - max

15 at 240 Vac Std. 1 Ph, 25 at 240 Vac Std. 3 Ph, 15 at 240 Vac TD 1 Ph, 60 at 240 Vac TD 3 Ph, 40 at 250 Vdc

NEMA rating

NEMA 3R

Voltage rating

240V

Miscellaneous

Product Category

Heavy Duty, Fusible with neutral

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - DH324NRK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)