



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

540 Mt Gallant Rd
29730-0000, SC Rock Hill
Phone: 803-263-6316
Fax: 000-000-0000



DH326FRK 600A/3P HD Fusible Safety Switch 240V Nema 3R

Eaton Corp

Catalog Number	DH326FRK
Manufacturer	Eaton Corp
Description	Eaton Enhanced Visible Blade Single-Throw Safety Switch, 600 A, Nema 3R, Painted Galvanized Steel, Class H, Three-Pole, Three-Wire, 240 V, Max HP: 75, 200 HP (3PH @STD, TD)), (1)#2-(1)600 Kcmil and (1)#1/0-(1)750 Kcmil Al
Weight per unit	152.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	600
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	240V

Dimensions and Weight

Depth	58
Height	12
Width	27.5

Descriptions

Description	600A/3P HD FUSIBLE SAFETY SWITCH 240V NEMA 3R
extra long description	ETN DH326FRK 600A/3P HD Fusible Sft
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Enhanced visible blade single-throw safety switch, 600 A, NEMA 3R, Painted galvanized steel, Class H, Three-pole, Three-wire, 240 V, Max Hp: 75, 200 hp (3PH @Std, TD)), (1)#2-(1)600 kcmil and (1)#1/0-(1)750 kcmil Al
Product Type	600A/3P HD Fusible Sfty SW 240V N3R

Manufacturer Information

Brand	Eaton
GTIN	00782113207407
Manufacturers Part Number	DH326FRK
UPC	782113207407

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

540 Mt Gallant Rd
29730-0000, SC Rock Hill
Phone: 803-263-6316
Fax: 000-000-0000

Packaging

Carton	1
Weight Per each	152

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	3R
standard	UL Listed