Eaton DH326NRK

Catalog Number: DH326NRK

Eaton Heavy duty single-throw fused safety switch, 600 A, NEMA 3R, Painted galvanized steel, Class H, Neutral, Three-pole, Fourwire, 240 V, Max Hp: 75, 200 hp (3PH @Std, TD)), (1)#2-(1)600 kcmil and (1)#1/0-(1)750 kcmil Al

General specifications



UPC Product Length/Depth

782113207421 12.84 in

Product Height Product Width 51.83 in 23.66 in

Product Weight Warranty

142 lb Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Compliances Certifications

NEC 230.62 (C) Compliant Barrier UL Listed





Physical Attributes

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

Type

Heavy duty fusible safety switch

Performance Ratings

Amperage Rating

600A

HP rating - max

75, 200 hp (3PH @Std, TD))

NEMA rating

NEMA 3R

Voltage rating

240V

Miscellaneous

Product Category

Heavy Duty, Fusible with neutral

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH326NRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia