

Eaton DH327NRK

Catalog Number: DH327NRK

Eaton Heavy duty single-throw fused safety switch, 800 A, NEMA 3R, Painted galvanized steel, Class L, Fusible with neutral, Three-pole, Four-wire, 240 V, Max Hp: 100 hp (3PH @Std), (4)#1/0-(4)750 kcmil Al



General specifications

Product Name	Catalog Number
Eaton heavy duty fusible safety switch	DH327NRK
UPC	Product Length/Depth
782113639253	57.5 in
Product Height	Product Width
12.38 in	27.5 in
Product Weight	Warranty
177 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
NEC 230.62 (C) Compliant Barrier	UL Listed

Physical Attributes

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse class provision

Class L

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type

Heavy duty fusible safety switch

Performance Ratings

Amperage Rating

800A

HP rating - max

100 hp (3PH @Std)

NEMA rating

NEMA 3R

Voltage rating

240V

Miscellaneous

Product Category

Heavy Duty, Fusible with neutral

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - DH327NRK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)