

Eaton DH361NGK

Catalog Number: DH361NGK

Eaton Heavy duty single-throw fused safety switch, 30 A, NEMA 1, Painted steel, Class H, Fusible with neutral, Three-pole, Four-wire, 600 V, Max Hp: 7.5, 10/ 15, 20 hp (1/3PH @480, 600 V), #14-#2 Cu/Al



General specifications

Product Name	Catalog Number
Eaton heavy duty fusible safety switch	DH361NGK
UPC	Product Length/Depth
782113205526	16.5 in
Product Height	Product Width
8.5 in	9.5 in
Product Weight	Warranty
20 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
NEC 230.62 (C) Compliant Barrier	UL Listed

Physical Attributes

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse class provision

Class H

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type

Heavy duty fusible safety switch

Wire size

#14-2 AWG Cu/Al

Performance Ratings

Amperage Rating

30A

HP rating - max

7.5, 10/ 15, 20 hp (1/3PH @480, 600 V)

NEMA rating

NEMA 1

Voltage rating

600 V

Miscellaneous

Product Category

Heavy Duty, Fusible with neutral

Resources

Brochures

[Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips](#)

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - DH361NGK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)