

Eaton DH361UDK

Catalog Number: DH361UDK

Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 30 A, NEMA 12, Painted galvanized steel, Non-Fusible, Three-pole, Three-wire, 3 at 240 Vac TD 1 Ph, 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 10 at 240 Vac TD 3 Ph

General specifications



Product Name	Catalog Number
Eaton heavy duty non-fusible safety switch	DH361UDK
	UPC
	782113205601

Product Length/Depth	Product Height
10.22 in	14.14 in

Product Width	Product Weight
8.76 in	17 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Certifications
UL Listed

Catalog Notes

Suitable for service entrance use with a neutral or ground lug kit installed. Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened.

Physical Attributes

Enclosure

NEMA 12

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Number Of Poles

Three-pole

Number of wires

3

Type

Single-throw

Performance Ratings

Amperage Rating

30A

HP rating - max

3 at 240 Vac TD 1 Ph, 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 10 at 240 Vac TD 3 Ph, 20 at 480 Vac TD 3 Ph, 30 at 600 Vac TD 3 Ph, 5 at 250 Vdc

NEMA rating

NEMA 12, NEMA 3R

Voltage rating

600 V

Miscellaneous

Product Category

Heavy Duty, Non-Fusible

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - DH361UDK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)