

# Eaton DH361UDKW

Catalog Number: DH361UDKW

Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 30 A, NEMA 12, Painted galvanized steel, Non-Fusible, Three-pole, Three-wire, 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 10 at 240 Vac TD 3 Ph

## General specifications



### Product Name

Eaton heavy duty non-fusible safety switch

### Catalog Number

DH361UDKW

### UPC

782114022696

### Product Length/Depth

10.22 in

### Product Height

14.14 in

### Product Width

8.76 in

### Product Weight

17 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

### Certifications

UL Listed

### Catalog Notes

For 2-pole applications; use outside poles of 3-pole switch. Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened.

## Physical Attributes

### Enclosure

NEMA 12

### Enclosure material

Painted galvanized steel

### Fuse configuration

Non-fusible

### Number Of Poles

Three-pole

### Number of wires

3

### Type

Enhanced visible blade

## Performance Ratings

### Amperage Rating

30A

### HP rating - max

7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 10 at 240 Vac TD 3 Ph, 20 at 480 Vac TD 3 Ph, 30 at 600 Vac TD 3 Ph, 5 at 250 Vdc

### NEMA rating

NEMA 12, NEMA 3R

### Voltage rating

600 V

## Miscellaneous

### Product Category

Heavy Duty, Non-Fusible

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - DH361UDKW](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)