

# Eaton DH361UGK

Catalog Number: DH361UGK

Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 30 A, NEMA 1, Painted steel, Three-pole, Three-wire, 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 10 at 240 Vac TD 3 Ph, 20 at 480 Vac TD 3 Ph



## General specifications

### Product Name

Eaton heavy duty non-fusible safety switch

### Catalog Number

DH361UGK

### UPC

782113205502

### Product Length/Depth

9.89 in

### Product Height

15.81 in

### Product Width

8.81 in

### Product Weight

17 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

### Certifications

UL Listed

### Catalog Notes

Suitable for service entrance use with a neutral or ground lug kit installed

## Physical Attributes

### Enclosure

NEMA 1

### Enclosure material

Painted steel

### Fuse configuration

Non-fusible

### Number Of Poles

Three-pole

### Number of wires

3

### Type

Single-throw

## Performance Ratings

### Amperage Rating

30A

### HP rating - max

7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 10 at 240 Vac TD 3 Ph, 20 at 480 Vac TD 3 Ph, 30 at 600 Vac TD 3 Ph, 5 at 250 Vdc

### NEMA rating

NEMA 1

### Voltage rating

600 V

## Miscellaneous

### Product Category

Heavy Duty, Non-Fusible

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - DH361UGK](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)