Eaton DH362FGK

Catalog Number: DH362FGK

Eaton Custom single-throw fused safety switch, 60 A, NEMA 1, Painted steel, Class H, Fusible without neutral, Three-pole, Threewire, 600 V, Max Hp: 20, 25/ 30, 50 hp (1/3PH @480, 600 V), #14-#2 Cu/Al

General specifications

Product Name Eaton custom single-throw fused safety switch	Catalog Number DH362FGK UPC 782113205977
Product Length/Depth 16.5 in	Product Height 8.5 in
Product Width 9.5 in	Product Weight 10 lb
Warranty Eaton Selling Policy 25-000, one (1) yea from the date of installation of the	Certifications r UL Listed
Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes Suitable for service entrance use with a Neutral Kit installed



Photo is representative



defaultTaxonomyAttributeLabel

Туре

Heavy duty fusible safety switch

Amperage Rating

60A

Number Of Poles

Three-pole

Product Category Heavy Duty, Fusible without neutral

Voltage rating

600 V

HP rating - max 20, 25/ 30, 50 hp (1/3PH @480, 600 V)

Wire size #14-2 AWG Cu/AI

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

Number of wires

3



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Right Reserved.

Eaton is a registered trademark.

Eaton.com All other trademarks are © 2024 Eaton. All Rights property of their respective Reserved. owners.



Eaton.com/socialmedia

Resources

Brochures

Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips

Catalogs Eaton's Volume 2—Commercial Distribution

Specifications and datasheets Eaton Specification Sheet - DH362FGK