# Eaton DH362NGK

## Catalog Number: DH362NGK

Eaton Heavy duty single-throw fused safety switch, 60 A, NEMA 1, Painted steel, Class H, Fusible with neutral, Three-pole, Four-wire, 600 V, Max Hp: 20, 25/ 30, 50 hp (1/3PH @480, 600 V), #14-#2 Cu/Al

### General specifications



DH362NGK

UPC

Product Length/Depth

Catalog Number

782113206035

5.25 in

**Product Height** 

Product Width

15.81 in

7.75 in

**Product Weight** 

Warranty

20 lb

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Compliances

Certifications

NEC 230.62 (C) Compliant Barrier

**UL** Listed



#### **Physical Attributes**

**Enclosure** 

NEMA 1

**Enclosure material** 

Painted steel

Fuse class provision

Class H

Fuse configuration

Fusible with neutral

**Number Of Poles** 

Three-pole

Number of wires

Type

Heavy duty fusible safety switch

#### Performance Ratings

Amperage Rating

60A

HP rating - max

20, 25/30, 50 hp (1/3PH @480, 600 V)

**NEMA** rating

NEMA 1

Voltage rating

600 V

#### Miscellaneous

#### **Product Category**

Heavy Duty, Fusible with neutral

#### Resources

#### **Brochures**

Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips

#### Catalogs

Eaton's Volume 2—Commercial Distribution

#### **Drawings**

95-955.dwg.pdf

Specifications and datasheets

Eaton Specification Sheet - DH362NGK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia