



Powering Business Worldwide

pe.eaton.com

Eaton enhanced visible blade single-throw fused safety switch

DH362NRK

UPC:782113206059

Dimensions:

- **Height:** 8.25 IN
- **Length:** 16.5 IN
- **Width:** 9.25 IN

Weight:20 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Heavy duty fusible safety switch
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Product Category:** Heavy Duty, Fusible with neutral
- **Voltage Rating:** 600V
- **Max Hp Rating:** 20, 25/ 30, 50 hp (1/3PH @480, 600 V)

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips](#)
- [Eaton Specification Sheet - DH362NRK](#)

Certifications:



- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.